

Load ring VWBM 1,8t-M20

Artikel-Nr: 7911439




The first and currently only lifting point from RUD which provides an internal thread to be used for rotating and turning even under load.

- Ball bearing for a shock-free rotating and turning with less friction.
- Lifting points pivots 360°.
- Suspension ring with enlarged pivoting area.
- Patented markings for easy determination for withdraw of service as well as the determination of the load angle.
- Rotatable at nominal WLL, 90° to the bolt-on direction.
- Large distance between bolt-on surface and load to avoid damage.
- Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.
- Minimum grade 10.9
- min. thread engagement length 1,1 x M
- max. thread engagement length 1.6 x M

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load ring VWBM 1,8t-M20

Artikel-Nr: 7911439



weight	1.76 kg	3.88 lbs
Nominal WLL	1800 kg	3960 lbs
T	158 mm	6-1/4"
A	13 mm	1/2"
B	54 mm	2-1/8"
C	35 mm	1-3/8"
D	62 mm	2-7/16"
E	55 mm	2-5/32"
F	25 mm	63/64"
G	88 mm	3-15/32"
H	34 mm	1-11/32"
M	M20 mm	M20