

Load ring VLBG-PLUS 10t M42 with RUD-bolt

Artikel-Nr: 7983554




- **Lifting points pivots 360°. Suspension ring pivots 180°**
- **Captive but exchangeable RUD-Bolt** with special corrosion protection Corrud-DT. Original RUD-Bolt is available as a spare part. Clear marking at the bolt head: RUD, thread size, batchno., class of strength.
- **Clamping spring** works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lifting mean possible respectively flat design if turned down.
- **Clear marking of the minimum WLL** for all loading directions.
- Available as:
 - Standard Metric Thread (DIN EN 13)
 - Metric Fine Thread (DIN EN 13)
 - Coarse Pitch Thread UNC (ANSI B1.1)
 - Fine Thread UNF (ANSI B1.1)
- Variable bolt lengths available for tapped or through holes.
- Tested and certified by DGUV Testing specifications: GS-HM-36:2021-09
Certificate No.: HM 220053
- Quick and easy installation with just one bolt connection.
- Assembly with flat / ring wrench or allen key possible.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning Actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load ring VLBG-PLUS 10t M42 with RUD-bolt

Artikel-Nr: 7983554



weight	6.60 kg	14.55 lbs
Nominal WLL	10000 kg	22040 lbs
T	196 mm	7-3/4"
A	77 mm	3"-1/32"
B	122 mm	4-13/16"
C	82 mm	3-1/4"
D	70 mm	2-3/4"
E	94 mm	3-11/16"
F	26,5 mm	1-3/64"
G	77 mm	3"-1/32"
H	73 mm	2-7/8"
I	205 mm	8-1/16"
K	113 mm	4-11/32"
L	150 mm	5-7/8"
M	M42 mm	M42
N	79 mm	2-3/4"