

## Excavator hook VCGH-G 16

Artikel-Nr: 7984048




Threaded Excavator hook for all lifting means.

- Can be combined with most commercial lifting means without additional connecting element.
- ICE-Bolt made out of patented steel. Non-hazardous deep temperature usage down to  $-60^{\circ}$ ; higher toughness and therefore higher bending strength as well as less wear occurrence.
- Robust, forged safety latch.
- Assembly with flat / ring wrench or allen key possible.
- Area of application in ring plane:  $45^{\circ}$ , Area of application at lateral load:  $+15^{\circ}$ ,  $-15^{\circ}$
- corresponds with the test criteria: "GS-HM-36"

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## Excavator hook VCGH-G 16

Artikel-Nr: 7984048



<b>weight</b>	8.49 kg	18.72 lbs
<b>Nominal WLL</b>	10000 kg	22040 lbs
<b>T</b>	49 mm	1-15/16"
<b>A</b>	15 mm	19/32"
<b>B</b>	141 mm	5-9/16"
<b>C</b>	200 mm	7-7/8"
<b>D</b>	220 mm	8-11/16"
<b>E</b>	170 mm	6-11/16"
<b>F</b>	48 mm	1-7/8"
<b>G</b>	120 mm	4-3/4"
<b>H</b>	150 mm	5-7/8"
<b>I</b>	70 mm	2-3/4"
<b>L</b>	35 mm	1-3/8"
<b>M</b>	M24 mm	M24
<b>N</b>	16 mm	null