

Excavator hook VCGH-G 22

Artikel-Nr: 7984313




Threaded Excavator hook for all lifting means.

- Can be combined with most commercial lifting means without additional connecting element.
- ICE-Bolt made out of patented steel. Non-hazardous deep temperature usage down to -60° ; higher toughness and therefore higher bending strength as well as less wear occurrence.
- Robust, forged safety latch.
- Assembly with flat / ring wrench or allen key possible.
- Area of application in ring plane: 45° , Area of application at lateral load: $+15^{\circ}$, -15°
- corresponds with the test criteria: "GS-HM-36"

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Excavator hook VCGH-G 22

Artikel-Nr: 7984313



weight	18.90 kg	41.67 lbs
Nominal WLL	20000 kg	44090 lbs
T	74 mm	2-29/32"
A	20 mm	3/4"
B	196 mm	7-23/32"
C	276 mm	10-7/8"
D	292 mm	11-1/2"
E	240 mm	9-1/2"
F	63 mm	2-15/32"
G	150 mm	5-7/8"
H	110 mm	4-11/32"
I	92 mm	3-5/8"
L	30 mm	1-3/16"
M	M24 mm	M24
N	22 mm	null