

## PowerPoint WPP-S-8t

Artikel-Nr: 7989948




Weldable universal hook connection for ring assemblies, round slings, wire ropes, hook assemblies

- Can be combined with most commercial lifting means without additional connecting element.
- Double ball bearing is the optimal solution for turning and flipping operations under full load.
- Lifting points pivots 360°.
- Parallel to the weld-on surface under nominal WLL.
- Large distance between bolt-on surface and load to avoid damage.
- Ideal connection link for crossbar construction.
- Lowest kinking possibility due to cardan joint.
- Clear marking of the minimum WLL for all loading directions.
- Requirements of the DIN 18800 are fulfilled by the weld arrangement (circular fillet weld), this means non occurrence of contact/crevice corrosion due to the endless weld seam (therefore suitable for outdoor constructions). The circular weld seam HY 3 + 10 requires only a small welding volume.
- Compact design and high wear resistancy due to the usage of high tensile material. ●Material of weld-on-block 1.6541 (23MnNiCrMo52) (please observe user instruction).
- The WLL statement corresponds to the minimum WLL in all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart).
- Significant product characteristics of the WPP-S, WPP-B, WPP-VIP, WPPH-S, WPPH-B and WPPH-VIP are subject to property right claims.
- Component according to the test criterias of DGUV "GS-HM-36".
- Simple and fast welding installation.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## PowerPoint WPP-S-8t

Artikel-Nr: 7989948



<b>weight</b>	8.20 kg	18.08 lbs
<b>Nominal WLL</b>	8000 kg	17630 lbs
<b>T</b>	310 mm	12-3/16"
<b>A</b>	49 mm	1-15/16"
<b>B</b>	208 mm	8-3/16"
<b>C</b>	48 mm	1-7/8"
<b>D</b>	100 mm	3-15/16"
<b>G</b>	102 mm	4"