

PowerPoint WPP-VIP16-8t

Artikel-Nr: 7989965




- Can be combined with most commercial lifting means without additional connecting element.
- Double ball bearing is the optimal solution for turning and flipping operations under full load.
- Lifting points pivots 360°.
- Parallel to the weld-on surface under nominal WLL.
- Large distance between bolt-on surface and load to avoid damage.
- Universal and non-mix-up clevis connection for easy construction with chains, hooks and eye.
- Lowest kinking possibility due to cardan joint.
- Clear marking of the minimum WLL for all loading directions.
- Requirements of the DIN 18800 are fulfilled by the weld arrangement (circular fillet weld), this means non occurrence of contact/crevice corrosion due to the endless weld seam (therefore suitable for outdoor constructions). The circular weld seam HY 3 + 10 requires only a small welding volume.
- Compact design and high wear resistancy due to the usage of high tensile material.
- Material of weld-on-block 1.6541 (23MnNiCrMo52) (please observe user instruction).
- The WLL statement corresponds to the minimum WLL in all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart).
- Significant product characteristics of the WPP-S, WPP-B, WPP-VIP, WPPH-S, WPPH-B and WPPH-VIP are subject to property right claims.
- Component according to the test criterias of DGUV "GS-HM-36".
- Simple and fast welding installation.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

PowerPoint WPP-VIP16-8t

Artikel-Nr: 7989965



| | | |
|--------------------|---------|-----------|
| weight | 4.41 kg | 9.72 lbs |
| Nominal WLL | 8000 kg | 17630 lbs |
| T | 102 mm | 4" |
| A | 16 mm | 5/8" |
| C | 100 mm | 3-15/16" |
| D | 100 mm | 3-15/16" |