

PowerPoint WPPH-VIP13-5t

Artikel-Nr: 7989986



- Large distance between bolt-on surface and load to avoid damage.
- Ideal connection link for crossbar construction.
- Universal and non-mix-up clevis connection for easy construction with chains, hooks and eye.
- Lowest kinking possibility due to cardan joint.
- Clear marking of the minimum WLL for all loading directions.
- Requirements of the DIN 18800 are fulfilled by the weld arrangement (circular fillet weld), this means non occurrence of contact/crevice corrosion due to the endless weld seam (therefore suitable for outdoor constructions). The circular weld seam HY 3 + 8 requires only a small welding volume.
- Compact design and high wear resistancy due to the usage of high tensile material. ●Material of weld-on-block 1.6541 (23MnNiCrMo52) (please observe user instruction).
- The WLL statement corresponds to the minimum WLL in all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart).
- Significant product characteristics of the WPP-S, WPP-B, WPP-VIP, WPPH-S, WPPH-B and WPPH-VIP are subject to property right claims.
- Component according to the test criterias of DGUV "GS-HM-36".
- Simple and fast welding installation.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

PowerPoint WPPH-VIP13-5t

Artikel-Nr: 7989986



weight	2.65 kg	5.84 lbs
Nominal WLL	5000 kg	11000 lbs
T	79 mm	3-1/8"
A	13 mm	1/2"
D	83 mm	3-1/4"