

VRBS Welding block VASK 16t

Artikel-Nr: 7992008




The welding blocks are forged out of the material 1.0577+N (St 52-3) and are marked with the identification number of the permissible nominal WLL.

The distance lugs have a distance measurement function for the required spacing to the root weld. (approx. 3mm) Welding should be carried out by a qualified person according to ISO 9606-1.

The joint faces must be free from impurities like oil, colour etc. The chosen welding point must be suitable for the corresponding force introduction. The engaging surface must be plain. Given an uneven surface, the weld blocks have to be re-adjusted. Root welding: Beginning of the root weld + fillet weld in the middle of the welding block.. Carefully clean the root before placing the covering weld seam.

VRBS Welding block VASK 16t

Artikel-Nr: 7992008



weight	1.30 kg	2.87 lbs
Nominal WLL	16000 kg	35270 lbs
T	39 mm	1-9/16"
A	130 mm	5-1/8"
C	57 mm	2-1/4"
F	57 mm	2-1/4"