

## Lashing Point Welding LPW-U 8000 daN with spring

Artikel-Nr: 7992226




### Original VIP-Quality

- Clear marking of the lashing capacity for all loading directions. LC marking with daN.
- Suspension ring pivots 180°.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks.
- The weld-on-block is made (forged) out of quality weldable steel.
- Clamping spring works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lashing mean possible.
- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Phosphated surface.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## Lashing Point Welding LPW-U 8000 daN with spring

Artikel-Nr: 7992226



<b>weight</b>	0.80 kg	1.76 lbs
<b>T</b>	83 mm	3-1/4"
<b>A</b>	42 mm	1-21/32"
<b>B</b>	87 mm	3-7/16"
<b>C</b>	31 mm	1-7/32"
<b>D</b>	51 mm	2"
<b>E</b>	52 mm	2-1/16"
<b>F</b>	18 mm	23/32"
<b>G</b>	46 mm	1-13/16"
<b>H</b>	16 mm	5/8"
<b>Lashing capacity</b>	8000 daN	null