

Lashing Point Welding LPW-U 13400 daN with spring

Artikel-Nr: 7992227




Original VIP-Quality

- Clear marking of the lashing capacity for all loading directions. LC marking with daN.
- Suspension ring pivots 180°.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks.
- The weld-on-block is made (forged) out of quality weldable steel.
- Clamping spring works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lashing mean possible.
- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Phosphated surface.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lashing Point Welding LPW-U 13400 daN with spring

Artikel-Nr: 7992227



weight	1.90 kg	4.19 lbs
T	117 mm	4-5/8"
A	61 mm	2-13/32"
B	115 mm	4-1/2"
C	44 mm	1-3/4"
D	67 mm	2-5/8"
E	73 mm	2-7/8"
F	24 mm	15/16"
G	60 mm	2-3/8"
H	22 mm	7/8"
Lashing capacity	13400 daN	null