

Lashing Point Welding LPW-U 20000 daN with spring

Artikel-Nr: 7992228




Original VIP-Quality

- Clear marking of the lashing capacity for all loading directions. LC marking with daN.
- Suspension ring pivots 180°.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks.
- The weld-on-block is made (forged) out of quality weldable steel.
- Clamping spring works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lashing mean possible.
- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Phosphated surface.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lashing Point Welding LPW-U 20000 daN with spring

Artikel-Nr: 7992228



weight	2.90 kg	6.39 lbs
T	126 mm	5"
A	75 mm	2-15/16"
B	129 mm	5-1/16"
C	55 mm	2-5/32"
D	67 mm	2-5/8"
E	71 mm	2-13/16"
F	26,5 mm	1-3/64"
G	60 mm	2-3/8"
H	26 mm	1"
Lashing capacity	20000 daN	null