

Load Ring VLBS 4t without spring

Artikel-Nr: 7993116




Universal Lifting point for welding with a diverse operating range in engineering and plant manufacturing.

- Suspension ring with optimised function form for a better support at side loading and protection of the clamping spring.
- Suspension ring pivots 180°.
- 100 % WLL at 90° in the load ring plane possible.
- Distance knobs at the weld-on block to achieve the necessary distance for the root weld.
- Clear marking of the minimum WLL for all loading directions.
- The weld-on-block is made (forged) out of a good weldable steel. Weld: HV 8 + a 3
- Tested and certified by DGUV, Testing specifications: GS-HM-36:2023-06, Certificate-No.: HM 240067
- Significant product characteristics of the VLBS are subject to property right claims.
- Confirmation of the deep temperature ability to -40°C by the notch bar impact test is on request possible (before order is placed).

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load Ring VLBS 4t without spring

Artikel-Nr: 7993116



weight	0.72 kg	1.59 lbs
Nominal WLL	4000 kg	8820 lbs
T	83 mm	3-1/4"
A	42 mm	1-21/32"
B	87 mm	3-7/16"
C	31 mm	1-7/32"
D	51 mm	2"
E	52 mm	2-1/16"
F	18 mm	23/32"
G	46 mm	1-13/16"
H	16 mm	5/8"