

Lashing Point Welding LPW 13400 daN without spring

Artikel-Nr: 7993144




Original VIP-Quality

- Lift bail can be pivoted through 180°.
- LC possible up to 90° in load ring plane.
- Clear indication of the lashing capacity in daN.
- Functionally optimised shape of the suspension ring for better support at side loading and protection of the clamping spring.
- Prepared for easy weld-on.
- Phosphated surface.
- Distance knobs on the weld-on block for the necessary distance for root welding.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lashing Point Welding LPW 13400 daN without spring

Artikel-Nr: 7993144



weight	1.90 kg	4.19 lbs
T	117 mm	4-5/8"
A	61 mm	2-13/32"
B	115 mm	4-1/2"
C	44 mm	1-3/4"
D	67 mm	2-5/8"
E	73 mm	2-7/8"
F	24 mm	15/16"
G	60 mm	2-3/8"
H	22 mm	7/8"
Lashing capacity	13400 daN	null