

## Lashing Point weldable LRBS 8000 daN

Artikel-Nr: 7993148




- Marked at the ring with the permitted lashing capacity "LC" in daN
- The distance lugs assist in achieving the correct air gap for the root of seam weld
- The material of the forged welding block is S355J2+N (1.0577+N)

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lashing points can be found in the specific user instruction.

## Lashing Point weldable LRBS 8000 daN

Artikel-Nr: 7993148



<b>weight</b>	0.77 kg	1.70 lbs
<b>T</b>	65 mm	2-9/16"
<b>A</b>	62 mm	2-7/16"
<b>B</b>	16 mm	5/8"
<b>C</b>	28 mm	1-1/8"
<b>D</b>	48 mm	1-7/8"
<b>E</b>	135 mm	5-5/16"
<b>F</b>	71 mm	2-13/16"
<b>Lashing capacity</b>	8000 daN	null