

## Load ring, for welding VRBS-FIX - 16t

Artikel-Nr: 7999301




The VRBS-FIX with considerable improvements !

- Split force introduction due to multiple point fixing.
- Suspension ring pivots 180°.
- 100% WLL at 90° in the load ring plane possible.
- Requirements of the DIN 18800 are fulfilled by the weld arrangement (circular fillet weld), this means non occurrence of contact/crevice corrosion due to the endless weld seam (therefore suitable for outdoor constructions). Weld: HY 9
- Clamping spring works as a noise reduction and holds the Oktagon-suspension ring in the requested position; therefore simple hinge of lifting mean possible.
- Patented markings for easy determination for withdraw of service. Patented markings for determination of the load angle.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks.
- Clear marking of the minimum WLL for all loading directions.
- The weld-on-block is made (forged) out of a quality weldable steel.
- Tested and certified by DGUV, Testing specifications: GS-HM-36:2021-09, Certificate-No.: HM 220056
- Significant product characteristics of the VRBS-FIX and VRBK-FIX are subject to property right claims.
- Simple and fast welding installation. Confirmation of the low temperature ability to -40°C by the notch bar impact test is possible upon request (before order is placed).

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## Load ring, for welding VRBS-FIX - 16t

Artikel-Nr: 7999301



<b>weight</b>	8.23 kg	18.14 lbs
<b>Nominal WLL</b>	16000 kg	35270 lbs
<b>T</b>	140 mm	5-1/2"
<b>A</b>	130 mm	5-1/8"
<b>B</b>	30 mm	1-3/16"
<b>C</b>	72 mm	2-27/32"
<b>D</b>	90 mm	3-17/32"
<b>E</b>	267 mm	10-1/2"
<b>F</b>	134 mm	5-9/32"