

Lashing Point for welding LRBS-FIX 8000 daN

Artikel-Nr: 7999303




- Clear marking of the minimum lashing capacity for all loading directions.
Lashing Capacity marking in daN.
- Suspension ring pivots 180°.
- Split force introduction due to multiple point fixing.
- Requirements of the DIN 18800 are fulfilled by the weld arrangement (circular fillet weld), this means non occurrence of contact/crevice corrosion due to the endless weld seam (therefore suitable for outdoor constructions).
- Clamping spring works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lifting mean possible.
- Patented markings for easy determination for withdraw of service.
- Easy painting due to fixing of the suspension ring.
- Simple and process safe positioning for the welding of pre-assembled components consisting of suspension ring and weld-on blocks.
- The weld-on-block is made (forged) out of a good weldable steel.
- Phosphated surface.
- Significant product characteristics of the LRBS-FIX and LRBK-FIX are subject to property right claims.

Welding should only be carried out by qualified persons according to ISO 9606-1. Other important RUD specific information and specialities to our RUD lashing points can be found in the specific user instruction.

Lashing Point for welding LRBS-FIX 8000 daN

Artikel-Nr: 7999303



weight	0.94 kg	2.07 lbs
T	74 mm	2-29/32"
A	60 mm	2-3/8"
B	14 mm	9/16"
C	39 mm	1-9/16"
D	48 mm	1-7/8"
E	132 mm	5-3/16"
F	69 mm	2-23/32"
Lashing capacity	8000 daN	null