

Lifting Point-Vario VWBG-V 3,5t-M27 (F=41 mm)

Artikel-Nr: 8600335




- Ball bearing for a shock-free rotating and turning with less friction.
- Lifting points pivots 360°.
- Suspension ring with enlarged pivoting area.
- Comprehensive range of threads and WLL (M8 – M30 bzw. 0,3 t – 5 t).
- Available as:
 - Standard Metric Thread (DIN EN 13)
 - Metric Fine Thread (DIN EN 13)
 - Coarse Pitch Thread UNC (ANSI B1.1)
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised(compare WLL chart / product information).
- Patented markings for easy determination for withdraw of service as well as the determination of the load angle.
- Rotatable at nominal WLL, 90° to the bolt-on direction.
- Variable bolt lengths available for tapped or through holes.
- RUD bolts with special corrosion protection Corrud-DT.
- Large distance between bolt-on surface and load to avoid damage.
- Non removable special bolt (this reduces the risk of improper standard bolts).
- corresponds with the test criteria: "GS-HM-36"
- Quick and easy installation with just one bolt Connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning Actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Lifting Point-Vario VWBG-V 3,5t-M27 (F=41 mm)

Artikel-Nr: 8600335



weight	2.65 kg	5.84 lbs
Nominal WLL	3500 kg	7700 lbs
T	173 mm	6-13/16"
A	18 mm	23/32"
B	66 mm	2-5/8"
C	40 mm	1-9/16"
D	81 mm	3-3/16"
E	70 mm	2-3/4"
F	41 mm	1-5/8"
G	88 mm	3-15/32"
M	M27 mm	M27