

Load ring VLBG-Z 2,5t 7/8"-9UNC with variable length

Artikel-Nr: 8600444




Fully captive 100% crack detected hexagon head cap bolts with thread lengths of H= 22-211mm are available. When ordering implicitly indicate the required length.

- **Lifting points pivots 360°. Suspension ring pivots 180°**
- **Captive but exchangeable RUD-Bolt** with special corrosion protection Corrod-DT. Original RUD-Bolt is available as a spare part. Clear marking at the bolt head: RUD, thread size, batchno., class of strength.
- **Clamping spring** works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lifting mean possible respectively flat design if turned down.
- **Clear marking of the minimum WLL** for all loading directions.
- Available as: - Standard Metric Thread (DIN EN 13) - Metric Fine Thread (DIN EN 13) - Coarse Pitch Thread UNC (ANSI B1.1) - Fine Thread UNF (ANSI B1.1)
- Variable bolt lengths available for tapped or through holes.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Quick and easy installation with just one bolt connection.
- Assembly with flat / ring wrench or allen key possible.
- Hand tightening with appropriate wrench is sufficient for a singular lift. Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load ring VLBG-Z 2,5t 7/8"-9UNC with variable length

Artikel-Nr: 8600444



Nominal WLL	2500 kg	5500 lbs
T	110 mm	4-11/32"
A	50 mm	1-31/32"
B	82 mm	3-1/4"
C	54 mm	2-1/8"
D	45 mm	1-25/32"
E	55 mm	2-5/32"
F	16,5 mm	21/32"
G	43 mm	1-11/16"
H	22-211 mm	7/8" up to 8-5/16"
I	113 mm	4-7/16"
K	64 mm	2-1/2"
L	65-254 mm	2-9/16" up to 10"
M	7/8"-9UNC mm	7/8"-9UNC
N	48 mm	1-7/8"