

Load ring VLBG-Z 4t 1"-8UNC with variable length

Artikel-Nr: 8600445




Fully captive 100% crack detected hexagon head cap bolts with thread lengths of H= 25-211mm are available. When ordering implicitly indicate the required length.

- **Lifting points pivots 360°. Suspension ring pivots 180°**
- **Captive but exchangeable RUD-Bolt** with special corrosion protection Corrod-DT. Original RUD-Bolt is available as a spare part. Clear marking at the bolt head: RUD, thread size, batchno., class of strength.
- **Clamping spring** works as a noise reduction and holds the suspension ring in the requested position; therefore simple hinge of lifting mean possible respectively flat design if turned down.
- **Clear marking of the minimum WLL** for all loading directions.
- Available as: - Standard Metric Thread (DIN EN 13) - Metric Fine Thread (DIN EN 13) - Coarse Pitch Thread UNC (ANSI B1.1) - Fine Thread UNF (ANSI B1.1)
- Variable bolt lengths available for tapped or through holes.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Quick and easy installation with just one bolt connection.
- Assembly with flat / ring wrench or allen key possible.
- Hand tightening with appropriate wrench is sufficient for a singular lift. Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Load ring VLBG-Z 4t 1"-8UNC with variable length

Artikel-Nr: 8600445



| Nominal WLL | 4000 kg | 8820 lbs |
|-------------|------------|--------------------|
| T | 125 mm | 4-15/16" |
| A | 50 mm | 1-31/32" |
| B | 82 mm | 3-1/4" |
| C | 54 mm | 2-1/8" |
| D | 45 mm | 1-25/32" |
| E | 67 mm | 2-5/8" |
| F | 18 mm | 23/32" |
| G | 43 mm | 1-11/16" |
| H | 25-211 mm | 1" up to 8-5/16" |
| I | 130 mm | 5-1/8" |
| K | 78 mm | 3-1/16" |
| L | 68-254 mm | 2-11/16" up to 10" |
| M | 1"-8UNC mm | 1"-8UNC |
| N | 48 mm | 1-7/8" |