

PowerPoint PP-S-5t-1 1/4"-7UNC

Artikel-Nr:

8600585




Can be combined with most commercial lifting means without additional connecting element.

- **Double ball bearings** is the optimal solution for turning and flipping operations under full load (not suitable for permanent turning under load).
- **Lifting points pivots 360°.**
- **Large distance between bolt-on surface and load to avoid damage.**
- **Rotatable at nominal WLL, 90° to the bolt-on direction** Lowest kinking possibility due to cardan joint.
- Clear marking of the minimum WLL for all loading directions.
- Marking with requested torque moment and nominal WLL with a safety factor of 4:1 (MRL 2006/42/EG) and 5:1 (ASME B 30.26).
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Significant product characteristics of the PP-S, PP-B and PP-VIP are subject to property right claims.
- The shape of the hook tip avoids unintentional attachment into small holes and tip loading. Robust, forged safety latch.
- Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

PowerPoint PP-S-5t-1 1/4"-7UNC

Artikel-Nr: 8600585



Nominal WLL	5000 kg	11000 lbs
T	267 mm	10-1/2"
A	37 mm	1-7/16"
B	174 mm	6-7/8"
C	40 mm	1-9/16"
D	95 mm	3-3/4"
E	85 mm	3-11/32"
F	30-45 mm	1 3/16" up to 1 3/4"
G	93 mm	3-21/32"
M	1 1/4"-7UNC mm	1 1/4"-7UNC