

## PowerPoint PP-B-4t-1"-8BSW

Artikel-Nr: 8600594




- **Double ball bearing** is the optimal solution for turning and flipping operations under full load (not suitable for permanent turning under load).
- **Lifting points pivots 360°.**
- **Large distance between bolt-on surface and load to avoid damage.**
- **Rotatable at nominal WLL, 90° to the bolt-on direction** Lowest kinking possibility due to cardan joint.
- **Suspension ring with enlarged pivoting area.**
- Clear marking of the minimum WLL for all loading directions.
- Marking with requested torque moment and nominal WLL with a safety factor of 4:1 (MRL 2006/42/EG) and 5:1 (ASME B 30.26).
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Significant product characteristics of the PP-S, PP-B and PP-VIP are subject to property right claims. ● Quick and easy installation with just one bolt connection.
- Hand tightening with appropriate wrench is sufficient for a singular lift.
- Please observe torque instructions when lifting point is permanently installed resp. at constant swivelling operations and tilting/ turning actions.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## PowerPoint PP-B-4t-1"-8BSW

Artikel-Nr: 8600594



<b>weight</b>	2.40 kg	5.29 lbs
<b>Nominal WLL</b>	4000 kg	8820 lbs
<b>T</b>	172 mm	6-25/32"
<b>A</b>	16 mm	5/8"
<b>B</b>	95 mm	3-3/4"
<b>C</b>	45 mm	1-25/32"
<b>D</b>	78 mm	3-1/16"
<b>E</b>	70 mm	2-3/4"
<b>F</b>	36 mm	1-27/64"
<b>G</b>	77 mm	3"-1/32"
<b>M</b>	1"-8BSW mm	1"-8BSW
<b>N</b>	20 mm	3/4"