

# Tools – Drill and Tap Combinations

## Drill and Tap Combinations

Metric and fractional drill and tap combination bits.

- High-speed steel
- Relief-ground
- 1/4" (6.35 mm) hexagonal shank
- Thread deburring
- For use with mild steel. 1.5x diameter max material thickness
- Approximate thread percentage - 75%



**US270014**

RUKO High-Speed Steel Metric Drill and Tap Combos										
Coarse Thread	Part Number	Pcs/Pkg	Price	Thread Size	Overall Length L1 (mm)	Drill Length S1 (mm)	Tap Length L2 (mm)	Drill Dia. D1 (mm)	Collar Dia. D2 (mm)	Max Material Thickness (mm)
		<b>US270014</b>	1	Retired	M3x0.5	51.0	5.0	7.0	2.5	7.0

