

Product availability: Stock - Normally stocked in distribution facility



Main

Range	TeSys
Device short name	LA4D
Poles description	3P
Product or component type	Interface module
Product compatibility	LC1D09...D115

Complementary

Mounting mode	Top mounted
Technology type	Solid state
[Us] rated supply voltage	24 V DC
Control circuit voltage limits	5...30 V 68 °F (20 °C) DC
[Ui] rated insulation voltage	250 V - control circuit IEC 60947-5-1
Connections - terminals	Control circuit connector 1 0.00...0.00 in ² (1...2.5 mm ²)flexible with cable end Control circuit connector 1 0.00...0.00 in ² (1...2.5 mm ²)flexible without cable end Control circuit connector 1 0.00...0.00 in ² (1...2.5 mm ²)solid with cable end Control circuit connector 1 0.00...0.00 in ² (1...2.5 mm ²)solid without cable end Control circuit connector 2 0.00...0.00 in ² (1...2.5 mm ²)flexible with cable end Control circuit connector 2 0.00...0.00 in ² (1...2.5 mm ²)flexible without cable end Control circuit connector 2 0.00...0.00 in ² (1...2.5 mm ²)solid with cable end Control circuit connector 2 0.00...0.00 in ² (1...2.5 mm ²)solid without cable end
[Ue] rated operational voltage	Control circuit 24...250 V AC Control circuit 380...415 V AC
Current consumption	8.5...15 mA 68 °F (20 °C)
Current state 0 guaranteed	<= 2 mA
Voltage state 0 guaranteed	< 2.4 V
Voltage state 1 guaranteed	5 V
Electrical durability	20 Mcycles 240 V
Local signalling	LED indicator
Height	0.75 in (19 mm)
Product weight	0.10 lb(US) (0.045 kg)

Environment

Standards	IEC 60255-5
Product certifications	CSA UL
Protection type	Built-in by diode
IP degree of protection	IP2x VDE 0106
Protective treatment	TH IEC 60068
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Permissible ambient air temperature around the device	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)

Heat dissipation	0.4 W control circuit
Immunity to microbreaks	1 ms

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901261001
Package weight(Lbs)	0.05 kg (0.12 lb(US))
Returnability	Yes
Country of origin	TN

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------