

# LAG8N113P

Auxiliary contact block, TeSys Giga  
contactor, 1NO + 1NC, lateral face side  
mounting, push-in terminals L1/R1



## Main

Range compatibility	TeSys G LC1G
Range of Product	TeSys G
Range	TeSys
Device short name	LAG8N
Product or Component Type	Auxiliary contact block
Auxiliary contacts operation	Instantaneous
Pole contact composition	1 NO + 1 NC
Connections - terminals	Screw clamp terminals 0.00...0.00 in <sup>2</sup> (0.75... 2.5 mm <sup>2</sup> )solid stranded without cable end Screw clamp terminals 0.00...0.00 in <sup>2</sup> (0.75... 2.5 mm <sup>2</sup> )flexible with cable end

## Complementary

Mounting Location	Side
[Ui] rated insulation voltage	500 V IEC 60947-5-1 500 V CSA 500 V UL
[Ue] rated operational voltage	500 V AC 25...400 Hz
[Ith] conventional free air thermal current	10 A 140 °F (60 °C)
Irms rated making capacity	140 A AC IEC 60947-5-1 250 A DC IEC 60947-5-1
Permissible short-time rating	100 A 140 °F (60 °C) 1 s 120 A 140 °F (60 °C) 500 ms 140 A 140 °F (60 °C) 100 ms
Protection type	GG fuse 10 A
Mechanical durability	8 Mcycles
Minimum switching current	1 mA
Minimum switching voltage	17 V
Non-overlap time	1.5 Ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact
Insulation resistance	> 10 MOhm
Height	2.20 in (55.8 mm)
Width	0.61 in (15.4 mm)
Depth	3.34 in (84.8 mm)
Product Weight	0.11 lb(US) (0.05 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	EN/IEC 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-5-1 GB 14048.5
Product Certifications	CB Scheme CCC CULus CE UKCA EU-RO-MR by DNV-GL EAC
IP degree of protection	IP20 conforming to IEC 60529
Protective treatment	TH
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m)

## Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	I12
GTIN	03606481047892
Returnability	Yes

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	2.68 in (6.8 cm)
Package 1 Length	3.74 in (9.5 cm)
Package 1 Weight	2.01 oz (57.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	64
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	8.77 lb(US) (3.979 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product