



The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.



Main

Range	TeSys
Product name	TeSys D
Product or component type	Contacteur
Device short name	LC1D
Contacteur application	Motor control Resistive load
Utilisation category	AC-1 AC-4 AC-3
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	Power circuit <= 690 V AC 25...400 Hz Power circuit <= 300 V DC
[Ie] rated operational current	50 A 140 °F (60 °C)) <= 440 V AC AC-3 power circuit 80 A 140 °F (60 °C)) <= 440 V AC AC-1 power circuit
Motor power kW	15 kW 220...230 V AC 50/60 Hz AC-3) 22 kW 380...400 V AC 50/60 Hz AC-3) 30 kW 500 V AC 50/60 Hz AC-3) 33 kW 660...690 V AC 50/60 Hz AC-3) 25 kW 415 V AC 50/60 Hz AC-3) 30 kW 440 V AC 50/60 Hz AC-3) 11 kW 400 V AC 50/60 Hz AC-4)
Motor power HP (UL / CSA)	3 Hp 115 V AC 50/60 Hz 1 phase 7.5 Hp 230/240 V AC 50/60 Hz 1 phase 15 Hp 200/208 V AC 50/60 Hz 3 phase 15 Hp 230/240 V AC 50/60 Hz 3 phase 40 Hp 460/480 V AC 50/60 Hz 3 phase 40 hp 575/600 V AC 50/60 Hz 3 phase
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	110 V AC 50/60 Hz
Auxiliary contact composition	1 NO + 1 NC
[Uimp] rated impulse withstand voltage	6 kV IEC 60947
Overtoltage category	III
[Ith] conventional free air thermal current	10 A 140 °F (60 °C) signalling circuit 80 A 140 °F (60 °C) power circuit
Irms rated making capacity	140 A AC signalling circuit IEC 60947-5-1 250 A DC signalling circuit IEC 60947-5-1 900 A 440 V power circuit IEC 60947
Rated breaking capacity	900 A 440 V power circuit IEC 60947
[Icw] rated short-time withstand current	400 A 104 °F (40 °C) - 10 s power circuit 810 A 104 °F (40 °C) - 1 s power circuit 84 A 104 °F (40 °C) - 10 min power circuit 208 A 104 °F (40 °C) - 1 min power circuit 100 A - 1 s signalling circuit 120 A - 500 ms signalling circuit 140 A - 100 ms signalling circuit
Associated fuse rating	10 A gG signalling circuit IEC 60947-5-1 100 A gG <= 690 V type 1 power circuit 100 A gG <= 690 V type 2 power circuit
Average impedance	1.5 mOhm - Ith 80 A 50 Hz power circuit
[Ui] rated insulation voltage	Power circuit 600 V CSA Power circuit 600 V UL Signalling circuit 690 V IEC 60947-1 Signalling circuit 600 V CSA Signalling circuit 600 V UL Power circuit 690 V IEC 60947-4-1
Electrical durability	1.45 Mcycles 50 A AC-3 <= 440 V 1.1 Mcycles 80 A AC-1 <= 440 V

Power dissipation per pole	3.7 W AC-3 9.6 W AC-1
Safety cover	With
Mounting support	Rail Plate
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product certifications	CCC GOST UL LROS (Lloyds register of shipping) CSA DNV BV GL RINA
Connections - terminals	Control circuit screw clamp terminals 2 0.00... 0.00 in ² (1...2.5 mm ²)flexible with cable end Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²)flexible without cable end Control circuit screw clamp terminals 2 0.00... 0.01 in ² (1...4 mm ²)flexible without cable end Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²)flexible with cable end Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²)solid without cable end Control circuit screw clamp terminals 2 0.00... 0.01 in ² (1...4 mm ²)solid without cable end Power circuit screw connection 1 0.00...0.05 in ² (1... 35 mm ²)flexible without cable end Power circuit screw connection 2 0.00...0.04 in ² (1... 25 mm ²)flexible without cable end Power circuit screw connection 1 0.00...0.05 in ² (1... 35 mm ²)flexible with cable end Power circuit screw connection 2 0.00...0.04 in ² (1... 25 mm ²)flexible with cable end Power circuit screw connection 1 0.00...0.05 in ² (1... 35 mm ²)solid without cable end Power circuit screw connection 2 0.00...0.04 in ² (1... 25 mm ²)solid without cable end
Tightening torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2 Power circuit 70.81 lbf.in (8 N.m) EverLink BTR screw connectors 0.04...0.05 in ² (25...35 mm ²) hexagonal 0.16 in (4 mm) Power circuit 44.25 lbf.in (5 N.m) EverLink BTR screw connectors 0.00...0.04 in ² (1...25 mm ²) hexag- onal 0.16 in (4 mm)
Operating time	4...19 ms opening 12...26 ms closing
Safety reliability level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	6 Mcycles
Maximum operating rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.3...0.6 Uc AC 50/60 Hz 140 °F (60 °C) Operational 0.8...1.1 Uc AC 50 Hz 140 °F (60 °C) Operational 0.85...1.1 Uc AC 60 Hz 140 °F (60 °C)
Inrush power in VA	140 VA 60 Hz 0.75 68 °F (20 °C) 160 VA 50 Hz 0.75 68 °F (20 °C)
Hold-in power consumption in VA	13 VA 60 Hz 0.3 68 °F (20 °C) 15 VA 50 Hz 0.3 68 °F (20 °C)
Heat dissipation	4...5 W 50/60 Hz
Auxiliary contacts type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1
Signalling circuit frequency	25...400 Hz
Minimum switching current	5 mA signalling circuit
Minimum switching voltage	17 V signalling circuit
Non-overlap time	1.5 Ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Insulation resistance	> 10 MOhm signalling circuit

Environment

IP degree of protection	IP20 front face IEC 60529
Protective treatment	TH IEC 60068-2-30
Pollution degree	3
Ambient air temperature for operation	23...140 °F (-5...60 °C)
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Permissible ambient air temperature around the device	-40...158 °F (-40...70 °C) at Uc
Operating altitude	9842.52 ft (3000 m) without
Fire resistance	1562 °F (850 °C) IEC 60695-2-1
Flame retardance	V1 UL 94
Mechanical robustness	Vibrations contactor open2 Gn, 5...300 Hz Vibrations contactor closed4 Gn, 5...300 Hz Shocks contactor closed15 Gn for 11 ms Shocks contactor open10 Gn for 11 ms
Height	4.80 in (122 mm)
Width	2.17 in (55 mm)
Depth	4.72 in (120 mm)
Product weight	1.88 lb(US) (0.855 kg)

Ordering and shipping details

Category	22357 - CTR, TESYS D, OPEN, 40-65A AC
Discount Schedule	I12
GTIN	00785901934592
Package weight(Lbs)	0.95 kg (2.1 lb(US))
Returnability	Yes
Country of origin	ID

Offer Sustainability


Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide which is known to the State of California to cause Carcinogen harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions



(1) Minimum electrical clearance

LC1		D40A...D65A
a		55
b1	with LA4 D•2	–
	with LA4 DB3 or LAD 4BB3	136
	with LA4 DF, DT	157
	with LA4 DM, DW, DL	166
c	without cover or add-on blocks	118
	with cover, without add-on blocks	120
c1	with LAD N (1 contact)	–
	with LAD N or C (2 or 4 contacts)	150
c2	with LA6 DK10, LAD 6DK	163
c3	with LAD T, R, S	171
	with LAD T, R, S and sealing cover	175

Wiring

