

Product availability: Stock - Normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys U
Device short name	LUCD
Product or component type	Advanced control unit
Product specific application	Basic protection and advanced functions, communication
Product compatibility	LULC033 LULC08 LUFDA01 LUFCA00 LUFDA10 LUFN.. LULC15 ASILUFC51 ASILUFC5 LULC09 LUFW10 LULC07 LUFDH11 LUFV2 LULC031
Utilisation category	AC-41 AC-44 AC-43
Motor power kW	3 kW 690 V AC 50/60 Hz 1.5 kW 400...440 V AC 50/60 Hz 2.2 kW 500 V AC 50/60 Hz
Thermal protection adjustment range	1.25...5 A
[Uc] control circuit voltage	24 V DC
Thermal overload class	Class 20 40...60 Hz -13...158 °F (-25...70 °C) IEC 60947-6-2 Class 20 40...60 Hz -13...158 °F (-25...70 °C) UL 508

Complementary

Main function available	Protection against phase failure and phase imbalance Manual reset Protection against overload and short-circuit Earth fault protection
Mounting mode	Plug-in
Mounting location	Front side
Control circuit voltage limits	20...27 V DC 24 V in operation
Typical current consumption	130 mA 24 V DC I maximum while closing with LUB12 220 mA 24 V DC I maximum while closing with LUB32 60 mA 24 V DC I rms sealed with LUB12 80 mA 24 V DC I rms sealed with LUB32
Operating time	35 ms opening with LUB12 control circuit 35 ms opening with LUB32 control circuit 70 ms closing with LUB12 control circuit 70 ms closing with LUB32 control circuit
Load type	3-phase motor self-cooled
Tripping threshold	14.2 x Ir +/- 20 %

[Ui] rated insulation voltage	600 V UL 508 690 V IEC 60947-1 600 V CSA C22.2 No 14
[Uimp] rated impulse withstand voltage	6 kV IEC 60947-6-2
Safe separation of circuit	400 V SELV between the control and auxiliary circuits IEC 60947-1 400 V SELV between the control or auxiliary circuit and the main circuit IEC 60947-1

Environment

Heat dissipation	2 W control circuit with LUB12 3 W control circuit with LUB32
Immunity to microbreaks	3 ms
Immunity to voltage dips	70 % / 500 ms IEC 61000-4-11
Standards	UL 508 type E, with phase barrier EN 60947-6-2 IEC 60947-6-2 CSA C22.2 No 14 type E
Product certifications	ATEX UL GOST CCC CSA ABS BV DNV GL LROS (Lloyds register of shipping) ASEFA
IP degree of protection	IP20 front panel and wired terminals IEC 60947-1 IP20 other faces IEC 60947-1 IP40 front panel outside connection zone IEC 60947-1
Protective treatment	TH IEC 60068
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Operating altitude	6561.68 ft (2000 m)
Fire resistance	1760 °F (960 °C) parts supporting live components IEC 60695-2-12 1202 °F (650 °C) IEC 60695-2-12
Shock resistance	10 gn power poles open IEC 60068-2-27 15 gn power poles closed IEC 60068-2-27
Vibration resistance	2 gn 5...300 Hz power poles open IEC 60068-2-6 4 gn 5...300 Hz power poles closed IEC 60068-2-6
Resistance to electrostatic discharge	8 KV 3 in open air IEC 61000-4-2 8 kV 4 on contact IEC 61000-4-2
Resistance to radiated fields	9.14 V/m (10 V/m) 3 IEC 61000-4-3
Resistance to fast transients	2 KV 3 serial link IEC 61000-4-4 4 kV 4 all circuits except for serial link IEC 61000-4-4
Immunity to radioelectric fields	10 V IEC 61000-4-6

Ordering and shipping details

Category	22397 - TESYS U - CNTRL MOD(LUCA,LUCD)
Discount Schedule	I11
GTIN	00785901265603
Package weight(Lbs)	0.12 kg (0.26 lb(US))
Returnability	Yes
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------