



Main

Range	TeSys
Product or Component Type	Contactor coil
Device short name	LX1D6
Control circuit type	AC 60 Hz
[Uc] control circuit voltage	480 V AC 60 Hz
Average resistance	480 Ohm 68 °F (20 °C)
Inductance of closed circuit	23 H
Product Compatibility	LC1D80 LC1D95
Mechanical durability	10 Mcycles
Maximum operating rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.3...0.6 Uc 50/60 Hz 131 °F (55 °C) Operational 0.8...1.1 Uc 50 Hz 131 °F (55 °C) Operational 0.85...1.1 Uc 60 Hz 131 °F (55 °C)
Inrush power in VA	220 VA 60 Hz 0.75 68 °F (20 °C)
Hold-in power consumption in VA	22 VA 60 Hz 0.3 68 °F (20 °C)
Heat dissipation	6...10 W 50/60 Hz

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Net Weight	0.62 lb(US) (0.28 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	3389110208832
Nbr. of units in pkg.	1
Package weight(Lbs)	10.86 oz (308 g)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.17 in (5.5 cm)
Package 1 width	3.54 in (9 cm)
Package 1 Length	4.92 in (12.5 cm)
Unit Type of Package 2	S02
Number of Units in Package 2	16
Package 2 Weight	12.25 lb(US) (5.558 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide which is known to the State of California to cause Carcinogen harm. For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty

18 months
