


LXD3LE7

Contacteur coil, TeSys D, 208 V AC 60 Hz, for contactors D40A-D80A DT60A-DT80A



Main

Range	TeSys
Product or Component Type	Contacteur coil
Device short name	LXD3
Control circuit type	AC 60 Hz
[Uc] control circuit voltage	208 V AC 60 Hz
Average resistance	105 Ohm 68 °F (20 °C)
Inductance of closed circuit	6.22 H
Product Compatibility	LC1D40A...D80A LC2D40A...D80A LC1DT60A...DT80A
Mechanical durability	6 Mcycles
Maximum operating rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out 0.3...0.6 Uc 60 Hz 140 °F (60 °C) Operational 0.85...1.1 Uc 60 Hz 140 °F (60 °C)
Inrush power in VA	160 VA 60 Hz 0.75 68 °F (20 °C)
Hold-in power consumption in VA	15 VA 60 Hz 0.3 68 °F (20 °C)
Heat dissipation	4...5 W 60 Hz

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Net Weight	0.15 lb(US) (0.07 kg)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	3389118332744
Nbr. of units in pkg.	1
Package weight(Lbs)	5.64 oz (160 g)
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.28 in (5.8 cm)
Package 1 width	2.28 in (5.8 cm)
Package 1 Length	3.86 in (9.8 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------