



## Main

Range	Multi 9
Product name	Multi 9 GFP
Product or Component Type	Residual current circuit breaker (RCCB)
Device short name	GFP
Device Application	Distribution
Poles description	4P
Neutral position	Left
Line Rated Current	25 A 104 °F (40 °C) EN/IEC 61008-1
Network type	AC
Earth-leakage sensitivity	86 MA UL 1053 100 mA EN/IEC 61008-1
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A-SI (Super Immunised)
Utilisation category	AC-23A EN/IEC 61008-1

## Complementary

Network Frequency	50/60 Hz
[Ue] rated operational voltage	415 V AC 50 Hz 480Y/277 V AC 60 Hz
Residual current tripping technology	Voltage independent
Rated breaking and making capacity	Idm 1500 A EN/IEC 61008-1
Rated conditional short-circuit current	Inc 10 kA 100 A gG
[Ui] rated insulation voltage	440 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kVEN/IEC 61008-1
Contact position indicator	Yes
Control Type	Toggle
Local signalling	ON, OFF, fault trip
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 mm pitches	8
Height	3.19 in (81 mm)
Width	2.83 in (72 mm)
Depth	2.36 in (60 mm)
Net Weight	0.99 lb(US) (0.45 kg)
Color	Gray
Mechanical durability	20000 cycles
Locking options description	Padlocking in OFF position
Connections - terminals	Tunnel type terminals top or bottom) 0.00...0.04 in <sup>2</sup> (1...25 mm <sup>2</sup> ) AWG 18...AWG 3) - flexible Tunnel type terminals top or bottom) 0.00...0.05 in <sup>2</sup> (1...35 mm <sup>2</sup> ) AWG 18...AWG 2) - rigid Tunnel type terminals top or bottom) 0.00...0.04 in <sup>2</sup> (1...25 mm <sup>2</sup> ) AWG 18...AWG 3) - flexible with ferrule
Wire stripping length	0.55 in (14 mm) top or bottom
Tightening torque	30.98 lbf.in (3.5 N.m) top or bottom

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	EN/IEC 61008-1 UL 1053
Product certifications	IEC UL
IP degree of protection	IP20(IEC 60529 IP40 modular enclosure)IEC 60529
Pollution degree	3
Electromagnetic compatibility	8/20 µs impulse withstand, 3000 A EN/IEC 61008-1
Tropicalisation	2 IEC 60068-1
Relative humidity	95 % 131 °F (55 °C)
Ambient air temperature for operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)

## Ordering and shipping details

Category	00948 - M9 GEN 2 CB UL1077 / IEC
Discount Schedule	DE2
GTIN	3606481198518
Nbr. of units in pkg.	1
Package weight(Lbs)	12.35 oz (350 g)
Returnability	Yes
Country of origin	ES

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.62 in (9.2 cm)
Package 1 width	3.03 in (7.7 cm)
Package 1 Length	3.35 in (8.5 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Weight	21.91 lb(US) (9.937 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

## Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.