



### Main

Range	Spacial
Product or component type	Drive flush mounting kit
Accessory category	Mounting and fixing accessory
Product specific application	Process and utilities
Range compatibility	Altivar variable speed drive ATV630 Altivar variable speed drive ATV930 Spacial SF and SM enclosures 19.69 in (500 mm) x 11.81 in (300 mm) Spacial S3D enclosure 19.69 in (500 mm) x 11.81 in (300 mm)
Compatibility for Altivar Process 630-930, size:	2
Motor power kW	5.5 KW 220/240 V 7.5 KW 380/480 V 11 kW
Mounting location	1 back of enclosure mounting plate 2 inside enclosure
Kit composition	1 x mounting plate with flanges and integrated gasket, steel with anti-corrosive coating by screws and nuts 1 x fixing accessories 1 x drilling template 1 x instruction sheet 1 x edge protector profile, plastic

### Complementary

Permanent permissible load	16.98 lb(US) (7.7 kg)
Color	Grey (RAL 7035)
Height	External 16.54 in (420 mm) Cut-out 14.76 in (375 mm)
Width	External 10.43 in (265 mm) Cut-out 8.46 in (215 mm)
Depth	Wall-enclosure separation 0.87 in (22 mm)
Net Weight	4.24 lb(US) (1.922 kg)
Services	Configuration of enclosure pre-drilled back Factory installation drive flush mounting kit

### Environment

IP degree of protection	IP55 conforming to IEC 60529
-------------------------	------------------------------

### Ordering and shipping details

Category	22276 - ATV930 FRAMES 1 & 2
Discount Schedule	CP4E
GTIN	00785901016762
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.05 in (5.2 cm)
Package 1 width	11.26 in (28.6 cm)
Package 1 Length	16.93 in (43 cm)
Unit Type of Package 2	S04
Number of Units in Package 2	5
Package 2 Weight	23.80 lb(US) (10.797 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>