



circuit breaker 3VA5 UL Frame 800 breaking capacity class M 35 kA @ 480 V 3-pole, line protection TM230, FTAM, In=800 A overload protection Ir=800 A permanently set short-circuit protection Ii=5...10 x In nut keeper kit

| Model                                                                                                                      |                             |
|----------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| product brand name                                                                                                         | SETRON                      |
| product designation                                                                                                        | Molded-case circuit breaker |
| product designation / according to UL file                                                                                 | MMAS                        |
| design of the product                                                                                                      | System protection           |
| design of the load switch / according to UL 489 / Heating, Air Conditioning, and Refrigeration circuit breaker (HACR Type) | Yes                         |
| design of the load switch / according to UL 489 / High-Intensity-Discharge circuit breaker (HID Type)                      | No                          |
| design of the load switch / according to UL 489 / Switching Duty circuit breaker (SWD Type)                                | No                          |
| design of the overcurrent release                                                                                          | TM230                       |
| protection function of the overcurrent release                                                                             | LI                          |
| number of poles                                                                                                            | 3                           |
| General technical data                                                                                                     |                             |
| insulation voltage / rated value                                                                                           | 800 V                       |
| operating voltage / at DC / rated value                                                                                    | 750 V                       |
| operating voltage / at AC / rated value                                                                                    | 690 V                       |
| power loss [W] / maximum                                                                                                   | 210 W                       |
| power loss [W] / for rated value of the current / at AC / in hot operating state / per pole                                | 70 W                        |
| mechanical service life (operating cycles) / typical                                                                       | 10 000                      |
| electrical endurance (operating cycles) / at AC-1 / at 380/415 V                                                           | 5 800                       |
| electrical endurance (operating cycles) / at AC-1 / at 690 V                                                               | 4 000                       |
| electrical endurance (operating cycles) / at 480 V                                                                         | 5 800                       |
| electrical endurance (operating cycles) / at 600 V                                                                         | 4 000                       |
| product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof                      | No                          |
| product function                                                                                                           |                             |
| • communication function                                                                                                   | No                          |
| • other measurement function                                                                                               | No                          |
| Net Weight                                                                                                                 | 14.217 kg                   |
| Current                                                                                                                    |                             |
| marking / according to UL 489 / 100%-rated breaker                                                                         | No                          |
| operational current                                                                                                        |                             |
| • at 40 °C                                                                                                                 | 800 A                       |
| • at 45 °C                                                                                                                 | 783 A                       |

|                                                                                                                                              |                                                                                                                                                                |
|----------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at 50 °C</li> <li>• at 55 °C</li> <li>• at 60 °C</li> <li>• at 65 °C</li> <li>• at 70 °C</li> </ul> | 766 A<br>750 A<br>733 A<br>716 A<br>699 A                                                                                                                      |
| <b>Switching capacity according to IEC 60947</b>                                                                                             |                                                                                                                                                                |
| switching capacity class of the circuit breaker                                                                                              | M                                                                                                                                                              |
| maximum short-circuit current breaking capacity (I <sub>cu</sub> )                                                                           |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 690 V</li> </ul>                                         | 85 kA<br>55 kA<br>25 kA                                                                                                                                        |
| operating short-circuit current breaking capacity (I <sub>cs</sub> )                                                                         |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 690 V</li> </ul>                                         | 85 kA<br>55 kA<br>19 kA                                                                                                                                        |
| short-circuit current making capacity (I <sub>cm</sub> )                                                                                     |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 415 V</li> <li>• at 690 V</li> </ul>                                         | 187 kA<br>121 kA<br>52.5 kA                                                                                                                                    |
| design of short-circuit protection                                                                                                           | For switching power values in DC networks, see the 3VA molded case circuit breaker device manual; link to be found under Service & Support in the last chapter |
| <b>Switching capacity according to UL 489</b>                                                                                                |                                                                                                                                                                |
| current breaking capacity                                                                                                                    |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 480 V</li> <li>• at 600 V</li> </ul>                                         | 85 kA<br>35 kA<br>18 kA                                                                                                                                        |
| <b>Adjustable parameters</b>                                                                                                                 |                                                                                                                                                                |
| adjustable response value setting current (I <sub>r</sub> ) / of the L-trip / with I <sub>2t</sub> characteristic                            |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                               | 800 A<br>800 A                                                                                                                                                 |
| adjustable response value delay time (t <sub>r</sub> ) / for L-tripping / with I <sub>2t</sub> characteristic                                |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                               | 1 s<br>1 s                                                                                                                                                     |
| adjustable response value setting current (I <sub>i</sub> ) / for I-tripping                                                                 |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                               | 4 000 A<br>8 000 A                                                                                                                                             |
| adjustable setting current (I <sub>nN</sub> ) / for N-tripping                                                                               |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>                                                               | 0 A<br>0 A                                                                                                                                                     |
| product function / grounding protection                                                                                                      | No                                                                                                                                                             |
| <b>Mechanical Design</b>                                                                                                                     |                                                                                                                                                                |
| product component                                                                                                                            |                                                                                                                                                                |
| <ul style="list-style-type: none"> <li>• undervoltage release</li> <li>• voltage trigger</li> <li>• trip indicator</li> </ul>                | No<br>No<br>No                                                                                                                                                 |
| height [in]                                                                                                                                  | 12.91 in                                                                                                                                                       |
| height                                                                                                                                       | 328 mm                                                                                                                                                         |
| width [in]                                                                                                                                   | 8.27 in                                                                                                                                                        |
| width                                                                                                                                        | 210 mm                                                                                                                                                         |
| depth [in]                                                                                                                                   | 4.72 in                                                                                                                                                        |
| depth                                                                                                                                        | 120 mm                                                                                                                                                         |
| <b>Connections</b>                                                                                                                           |                                                                                                                                                                |
| arrangement of electrical connectors / for main current circuit                                                                              | Front connection                                                                                                                                               |
| type of electrical connection / for main current circuit                                                                                     | nut keeper kit on both ends                                                                                                                                    |
| type of connectable conductor cross-sections / for flat-bar terminal connection / minimum                                                    | 20 x 4 mm                                                                                                                                                      |
| type of connectable conductor cross-sections / for flat-bar                                                                                  | 50 x 28 mm                                                                                                                                                     |

|                                                                                       |        |
|---------------------------------------------------------------------------------------|--------|
| terminal connection / maximum                                                         |        |
| design of the surface / of the connections / on the bottom of the switch (N, 2, 4, 6) | silver |
| <b>Auxiliary circuit</b>                                                              |        |
| number of CO contacts / for auxiliary contacts                                        | 0      |
| <b>Accessories</b>                                                                    |        |
| product extension / optional / motor drive                                            | No     |
| <b>Environmental conditions</b>                                                       |        |
| protection class IP / on the front                                                    | IP40   |
| ambient temperature                                                                   |        |
| • during operation / minimum                                                          | -25 °C |
| • during operation / maximum                                                          | 70 °C  |
| • during storage / minimum                                                            | -40 °C |
| • during storage / maximum                                                            | 80 °C  |
| reference code / according to IEC 81346-2                                             | Q      |
| <b>Approvals / Certificates</b>                                                       |        |
| <b>General Product Approval</b>                                                       |        |



[Miscellaneous](#)



[Miscellaneous](#)



|                          |     |                   |                      |
|--------------------------|-----|-------------------|----------------------|
| General Product Approval | EMV | Test Certificates | Maritime application |
|--------------------------|-----|-------------------|----------------------|

[Confirmation](#)



[Type Test Certificates/Test Report](#)



|                      |       |
|----------------------|-------|
| Maritime application | other |
|----------------------|-------|



[Miscellaneous](#)

[Confirmation](#)

|                    |
|--------------------|
| <b>Environment</b> |
|--------------------|

[Environmental Confirmations](#)



|                            |
|----------------------------|
| <b>Further information</b> |
|----------------------------|

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA5580-5EC32-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA5580-5EC32-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[https://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA5580-5EC32-0AA0](https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA5580-5EC32-0AA0)

CAX-Online-Generator






<https://www.siemens.com/cax>

Tender specifications


<https://www.siemens.com/specifications>

Characteristic curves

[https://curves.simarisiemens.com/curves/<mmp\\_prod\\_noCOMP="HAUPT"></mmp\\_prod\\_no>](https://curves.simarisiemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>)



CB



last modified:

3/31/2025 

