

CODE NUMBER

0326008PK

DESCRIPTION

Standard


FEATURES

MIX-70-A Thermostatic Water Mixing Valve with the following features:


- 1/2" NPTF thread inlets
- Solid wax hydraulic principle thermostat assures dependable mixing of hot and cold water
- Inlet Temperatures: hot inlet, 120°F - 180°F (49°C - 82°C), cold inlet, 39°F - 85°F (4°C - 29°C)
- Minimum Supply Pressure Static: 30psi (207 kPa)
- Temperature Out: Field range: 80°F - 120°F (27°C - 49°C), adjustable
- Maximum Temperature: 200°F (93°C)
- Maximum Pressure: 150psi (1034 kPa)
- Minimum Flow: 0.5 gpm (1.9 lpm) @ 0.8psi (0.55 kPa)†
- Maximum Flow: 20 gpm (76 lpm) @ 125psi (862 kPa)†
- Maximum Pressure Differential between Hot & Cold Water Supplies: 25%
- Combination check stops on inlets to protect crossflow
- Thermostat controls both hot and cold water
- Lead Free* Brass body construction
- Adjustment cap with locking feature
- Integral filter washers and check valves
- ASSE Standard 1070 Certified
- Weight: 1.9 LBs (0.9 Kg)

NOTES

All information contained within this document subject to change without notice.



CAUTION: All thermostatic water-mixing valves have limitations. They will NOT provide the desired accuracy outside of their flow capacity range. Consult the Flow Capacity Chart and DO NOT OVERSIZE. Minimum flow must be no less than as indicated.



COMPLIANCES & CERTIFICATIONS



(cUPC Low Lead Compliant)

Sloan 10500 Seymour Ave, Franklin Park, IL 60131

Phone: 800.982.5839 • Fax: 800.447.8329 • sloan.com

Sloan 10500 Seymour Ave, Franklin Park, IL 60131
Phone: 800.982.5839 • Fax: 800.447.8329 • sloan.com