

Enclosed changeover switches

Motorised operation

RTSE - remote controlled from 40 to 3200 A

Three-phase ATyS M 3s /3e in steel enclosure



conf_305_b_1_cat

General characteristics

- ATyS 3s from 125 to 1600 A.
- ATyS 3e for ratings 2000, 2500 and 3200A.
- Adapted to mechanical risk and dust hazard.
- Protection degree: IP54.
- Colour: RAL 7035.
- Cable gland plate: top and bottom.
- Connection of cables: Top or bottom from 125 to 250 A, bottom from 400 to 3200 A.
- The auxiliary contacts are wired to a terminal block.
- Material: XC steel, thickness 2 mm.
- Coating: epoxy polyester powder.
- Wall mounting: 4 wall mounting brackets supplied loose (rating ≤ 400 A), floor standing feet (rating ≥ 630 A).
- Door: solid with hinges
- Locking system: 3 mm double bar key (key supplied)

References

Standard device - 230 VAC

Rating (A)	No. of poles	Reference
125	4 P	1723 4012
160	4 P	1723 4016
250	4 P	1723 4025
400	4 P	1723 4040
630	4 P	1723 4063
800	4 P	1723 4080
1000	4 P	1723 4100
1250	4 P	1723 4120
1600	4 P	1723 4160
2000	4 P	1723 4200
2500	4 P	1723 4250
3200	4 P	1723 4320

Accessories

Factory fitted

Description	Reference
Dual power supply	1599 9001
2 nd auxiliary contact: from 125 to 630 A	1599 9002
2 nd auxiliary contact: from 800 to 1600 A	1599 9012
Autotransformer 400/230 VAC for three-phase networks without neutral	see ATyS pages
Terminal shrouds	see ATyS pages
3 position padlocking (I-O-II)	1599 9003

Customer fit

Description: Conducting neutral	Reference
125 ... 160 A	1599 1006
250 A	1599 1025
400 A	1599 1040
630 A	1599 1063
800 A	1599 1080
1000 A	1599 1100
1250 A	1599 1120
1600 A	1599 1160