

# SIDER

Load break switches for power distribution  
with visible breaking from 125 to 1600 A

## References (continued)

### Side operation

Rating (A)	No. of poles	Switch body Direct operation	Switch body External right side operation	Direct handle	External handle	Shaft for external handle	Auxiliary contact
ND 125 A	3 P	2915 <b>3012</b>	2921 <b>3012</b>	Black 3629 <b>7901</b> <sup>(1)</sup>	S2 type Black IP55 1425 <b>2111</b> <sup>(1)</sup> Black IP65 1427 <b>2111</b> Red / Yellow IP65 1428 <b>2111</b>	200 mm 1400 <b>1020</b> <sup>(1)</sup>	1 <sup>st</sup> contact NO/NC 3999 <b>0021</b> <sup>(2)(3)</sup> 2 contacts NO/NC 3999 <b>0022</b> <sup>(2)(3)</sup> 1 contact NC 3999 <b>0701</b> <sup>(4)(6)</sup> 1 contact NO 3999 <b>0702</b> <sup>(4)(6)</sup>
	4 P	2915 <b>4012</b>	2921 <b>4012</b>				
ND 200 A	3 P	2915 <b>3021</b>	2921 <b>3020</b>				
	4 P	2915 <b>4021</b>	2921 <b>4020</b>				
ND 250 A	3 P	2915 <b>3025</b>	2921 <b>3025</b>				
	4 P	2915 <b>4025</b>	2921 <b>4025</b>				
ND 315 A	3 P	2915 <b>3031</b>	2921 <b>3031</b>				
	4 P	2915 <b>4031</b>	2921 <b>4031</b>				
ND 400 A	3 P	2915 <b>3041</b>	2921 <b>3041</b>				
	4 P	2915 <b>4041</b>	2921 <b>4041</b>				
ND 500 A	3 P	2915 <b>3051</b>	2921 <b>3051</b>				
	4 P	2915 <b>4051</b>	2921 <b>4051</b>				
630 A	3 P	2905 <b>3063</b>	2905 <b>3063</b>	Black 2799 <b>7052</b> <sup>(1)</sup> Conversion kit 2799 <b>7070</b> <sup>(5)</sup> Red 2799 <b>7053</b> Conversion kit 2799 <b>7070</b> <sup>(5)</sup>	S3 type Black IP65 1437 <b>3111</b> <sup>(1)</sup> Red / Yellow IP65 1438 <b>3111</b>	200 mm 1404 <b>1520</b> <sup>(1)</sup>	1 <sup>st</sup> contact NO/NC 2799 <b>0011</b> 2 <sup>nd</sup> contact NO/NC 2799 <b>0012</b>
	4 P	2905 <b>4063</b>	2905 <b>4063</b>				
800 A	3 P	2905 <b>3080</b>	2905 <b>3080</b>				
	4 P	2905 <b>4080</b>	2905 <b>4080</b>				
1250 A	3 P	2905 <b>3120</b>	2905 <b>3120</b>				
	4 P	2905 <b>4120</b>	2905 <b>4120</b>				
1600 A	3 P	2905 <b>3160</b>	2905 <b>3160</b>				
	4 P	2905 <b>4160</b>	2905 <b>4160</b>				

(1) Standard.

(2) Auxiliary signal contact - Type S.

(3) For direct operation.

(4) For external operation.

(5) Conversion kit necessary for any direct operation.

(6) Auxiliary signal contact - Type U.