

FUSOMAT

Visible breaking and tripping fuse switches
from 250 to 1250 A

References

NFC and DIN - Front operation - Switch body with a shunt trip coil - 230 VAC

Rating (A) Fuse	No. of poles	Switch body	Direct handle	External handle	Shaft for external handle	Auxiliary contact position	Auxiliary contact tripping	1 st Fuse blown AC	Terminal shrouds (1 piece)	Terminal screens top	Inter phase barrier										
250 A / 1	3 P	3650 3026	Black 3999 6201 ⁽¹⁾	S3 type Black IP55 1431 3511 ⁽¹⁾	200 mm 1401 1520	1 st contact NO/NC 3999 0051	1 contact NO/NC 3999 0031	3 P 3994 1304	3 P 3998 3040 ⁽²⁾												
	4 P	3650 6026																			
400 A / 2	3 P	3650 3041																			
	4 P	3650 6041																			
630 A / 3	3 P	3650 3064										S3 type Black IP55 1432 3511	320 mm 1401 1532 ⁽¹⁾	2 nd contact NO/NC 3999 0052			3 P 3994 1306	3 P 3998 3063 ⁽²⁾			
	4 P	3650 6064																			
800 A / 4	3 P	3650 3080																			
	4 P	3650 6080																			
1250 A / 4	3 P	3650 3121		Black 3999 6012 ⁽¹⁾					3 P 3994 1312	3 P 3998 3120 ⁽³⁾	3 P 2998 0003										
	4 P	3650 6121																			
	3 P																				
	4 P																				
	3 P																				
	4 P																				

(1) Standard.

(2) Top/bottom.

(3) Bottom terminals protection screen as standard.