

## References

### VM1 changeover switches I-0-II

Rating (A)	No. of poles	Switch body	Direct handle	External handle	Shaft for external handle	IP20 bridging bars <sup>(2)</sup>	Auxiliary contact
63 A	3 P	4430 <b>3006</b> <sup>(1)</sup>	Black 4439 <b>5012</b>	S1 type Black IP65 1413 <b>2113</b>	200 mm 1402 <b>0820</b> 320 mm 1402 <b>0832</b>	3 P 4499 <b>3006</b> 4 P 4499 <b>4006</b>	1 auxiliary contact NO/NC 4439 <b>0001</b>
	4 P	4430 <b>4006</b> <sup>(1)</sup>					
80 A	3 P	4430 <b>3008</b> <sup>(1)</sup>					
	4 P	4430 <b>4008</b> <sup>(1)</sup>					
100 A	3 P	4430 <b>3010</b> <sup>(1)</sup>					
	4 P	4430 <b>4010</b> <sup>(1)</sup>					
125 A	3 P	4430 <b>3012</b>					
	4 P	4430 <b>4012</b>					

(1) Available enclosed (see "Enclosed changeover switches" page 600).

(2) IP: protection degree according to IEC 60529 standard.

### VM1 changeover switches I - I+II - II

Rating (A)	No. of poles	Switch body	Direct handle	External handle	Shaft for external handle	IP20 bridging bars <sup>(1)</sup>
63 A	3 P	4440 <b>3006</b>	Black 4449 <b>5012</b>	S1 type Black IP65 1413 <b>2114</b>	200 mm 1403 <b>0820</b> 320 mm 1403 <b>0832</b>	3 P 4499 <b>3006</b> 4 P 4499 <b>4006</b>
	4 P	4440 <b>4006</b>				
80 A	3 P	4440 <b>3008</b>				
	4 P	4440 <b>4008</b>				
100 A	3 P	4440 <b>3010</b>				
	4 P	4440 <b>4010</b>				
125 A	3 P	4440 <b>3012</b>				
	4 P	4440 <b>4012</b>				

(1) IP: protection degree according to IEC 60529 standard.

## Accessories

### Direct operation handle

Rating (A)	Switching type	Reference
63 ... 125	I - 0 - II	4439 <b>5012</b>
63 ... 125	I - I+II - II	4449 <b>5012</b>



access\_111\_a\_1\_cat

### External operation handle

#### Use

Door interlocked external front operation handles include an escutcheon, are padlockable and must be utilised with an extension shaft.

Rating (A)	Switching type	padlockable	External IP <sup>(1)</sup>	Reference
63 ... 125	I - 0 - II	1 Position	IP55	1411 <b>2113</b>
63 ... 125	I - 0 - II	1 Position	IP65	1413 <b>2113</b>
63 ... 125	I - 0 - II	3 Positions	IP65	1413 <b>2813</b>
63 ... 125	I - I+II - II	1 Position	IP65	1413 <b>2114</b>
63 ... 125	I - I+II - II	3 Positions	IP65	1413 <b>2814</b>



access\_111\_a\_1\_cat

(1) IP: protection degree according to IEC 60529 standard.