

Profile C

References

W x H x e (mm)	Perforations (mm)	Perforation centres (mm)	Material	Profiles length (m)	To be ordered in multiples of	Reference
20 x 14 x 1.5	8.2 x 40	50	Steel z-b ⁽¹⁾	3	30 m	5000 0120
30 x 15 x 1.5	8.2 x 40	50	Steel z-b ⁽¹⁾	3	30 m	5000 0121
35 x 35 x 2	8.2 x 40	50	Steel z-b ⁽¹⁾	2	12 m	5000 0132
35 x 35 x 2	8.2 x 40	50	Steel z-b ⁽¹⁾	3	18 m	5000 0122
30 x 15 x 1.5	6.3 x 18	50	Stainless steel	2	10 m	5000 1021
20 x 15 x 2	without		Aluminium	2	10 m	SA12 4202
20 x 15 x 2	without		Aluminium	3	15 m	SA13 4202
20 x 15 x 2	without		Aluminium	6	30 m	SA10 4202
29 x 19 x 2.5	without		Aluminium	2	10 m	SA12 4201
29 x 19 x 2.5	without		Aluminium	3	15 m	SA13 4201
29 x 19 x 2.5	without		Aluminium	6	30 m	SA10 4201





(1) White zinc-coated.



Accessories

Screws

Type	Insert M	Dimensions H x W (mm)	For profiles	To be ordered in multiples of	Reference
Rhomboidal nut	M3	15.5 x 15.5	20 x 14	100	5000 0023
Rhomboidal nut	M4	15.5 x 15.5	20 x 14	100	5000 0024
Rhomboidal nut	M5	15.5 x 15.5	20 x 14	100	5000 0025
Rhomboidal nut	M6	15.5 x 15.5	20 x 14	100	5000 0026
Rhomboidal nut	M8	15.5 x 15.5	20 x 14	100	5000 0028
Rhomboidal nut	M8	25 x 25	30 x 15	100	5000 0029
Square nut	M8	35 x 28	35 x 35	100	5000 0037
Square nut	M18	35 x 28	35 x 35	100	5000 0039
Rhomboidal nut	M3	33 x 11	30 x 15	100	5000 0033
Rhomboidal nut	M4	33 x 11	30 x 15	100	5000 0034
Rhomboidal nut	M5	33 x 11	30 x 15	100	5000 0035
Rhomboidal nut	M6	34 x 20	35 x 35	100	5000 0036
Rhomboidal nut	M8	34 x 20	35 x 35	100	5000 0038
Straddle bracket	Ø 8.2		20 x 14	100	5000 0010
Straddle bracket	Ø 8.2		30 x 15	100	5000 0011
Straddle bracket	Ø 8.2		35 x 35	100	5000 0012



Foam

Type	l x e (mm)	To be ordered in multiples of	Reference
Roll of 60 meter foam ⁽¹⁾	20 x 12	1	5000 0057
Roll of 60 meter foam ⁽¹⁾	25 x 12	1	5000 0058

(1) Enables to maintain nuts for symmetrical profiles.

