

# SpinMeister® Precleaners

## Extreme Duty Filtration


### Technical Specifications

- Temp (continuous): min -60°F (-51°C), max 250°F (121°C)
- 85%+ removal efficiency standard to 15 microns
- Heavy duty vibration resistant stainless steel clamp

### Molded SpinMeister®

- Molded fiber filled composite housing
- Plastic rotors
- To be used with Solberg Inlet SpinMeister® Filter Assemblies

Part Number	SCFM Flow Rating Range	Slip Fit Outlet	Dimensions (inches)		
			H.T.	Slip Fit I.D.	Cover O.D.
SM-1.5	3-20	1.5"	2.25	1.50	3.63
SM-2	20-110	2"	3.06	2.00	4.78
SM-3	75-250	3"	4.03	3.00	7.13
SM-4	250-400	4"	5.38	4.00	9.63
SM-6	450-900	6"	7.00	6.00	12.25



SpinMeister® Airflow Schematic

### Aluminum SpinMeister®

- Polished aluminum housing
- Stainless steel rotors
- To be used with Solberg Inlet SpinMeister® Filter Assemblies

Part Number	SCFM Flow Rating Range	Slip Fit Outlet	Dimensions (inches)		
			H.T.	Slip Fit I.D.	Cover O.D.
SMA-2	10-110	2"	3.02	2.05	4.80
SMA-3	140-300	3"	4.80	3.00	8.50
SMA-4	140-350	4"	4.80	4.00	8.50
SMA-6	400-850	6"	7.33	6.00	12.25
SMA-9	900-2000	9"	8.13	9.00	17.13

### SpinMeister® for Vacuum

- Low pressure drop design
- Molded fiber filled composite housing
- Stainless steel rotors
- To be used with Solberg Vacuum Filter Series

Part Number	SCFM Flow Rating Range	Slip Fit Outlet	Dimensions (inches)		
			H.T.	Slip Fit I.D.	Cover O.D.
SML235	40-110	3.5"	4.05	3.45	7.39
SML345	100-200	4.5"	5.57	4.53	10.23
SML445	200-450	4.5"	7.19	4.53	10.23

### Learn More

For more information about Solberg products and finding the right solutions for your equipment needs, visit us at [SolbergMfg.com](http://SolbergMfg.com).

### Contact Us

[solbergmfg.com/locations](http://solbergmfg.com/locations)

