

**Part No:** 3765-813

**Fabricated DWV**

**Glue-on Saddles**

**Desc:** 20X3 PVC STUB SADDLE SOC SCH40 N.P.R.

**MSRP:** 275.12

**Part Code:** 390

**Weight(lbs):** 2.976

**Weight(kg):** 1.35

**Weight(gm):** 1350

**Size:** 20 X 3

**Color:** WHITE

**Material:** PVC

**Schedule** SCH 40 DWV Stub Saddle

**Connection** Socket



**H** = 15-1/4

**L** = 11-1/2

**M** = 3-15/16

**N** = 3

## Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  inch & larger  $\pm 1/2$  inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.
- L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.
- M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.
- N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.
- W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

