

**Part No:** 3775-794

**Fabricated DWV**

**Wyes**

**Desc:** 18X14 PVC RED WYE SOC SCH40 N.P.R.

**MSRP:** 2543.02

**Part Code:** 390

**Weight(lbs):** 97.224

**Weight(kg):** 44.1

**Weight(gm):** 44100

**Size:** 18 X 14


**Color:** GRAY

**Material:** PVC

**Schedule** SCH 40 DWV

**Connection** Socket X Socket X Socket

**Type** Reducing Wye



|                   |                    |                      |                      |                   |
|-------------------|--------------------|----------------------|----------------------|-------------------|
| <b>G1</b> = 5-3/8 | <b>G2</b> = 23-3/8 | <b>G3</b> = 23-13/16 | <b>H3</b> = 30-13/16 | <b>L</b> = 46-3/4 |
| <b>M</b> = 19-1/8 | <b>M1</b> = 14-7/8 | <b>H1</b> = 14-3/8   | <b>H2</b> = 32-3/8   |                   |

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

