

**Part No:** 3775-908

**Fabricated DWV**

**Wyes**

**Desc:** 24X8 PVC RED WYE SOC SCH40 N.P.R.

**MSRP:** 3214.11

**Part Code:** 390

**Weight(lbs):** 143.301

**Weight(kg):** 65

**Weight(gm):** 65000

**Size:** 24 X 8


**Color:** WHITE

**Material:** PVC

**Schedule** SCH 40 DWV

**Connection** Socket X Socket X Socket

**Type** Reducing Wye



**G1** = 1/4

**G2** = 24-1/4

**G3** = 24-5/8

**H3** = 28-7/8

**L** = 48-1/2

**M** = 25-3/8

**M1** = 9-1/4

**H1** = 12-1/4

**H2** = 36-1/4

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

