

**Part No:** 3777-764

**Fabricated DWV**

**Combo Wye & 1/8 Bend**

**Desc:** 16X14 PVC RD CMB Y&1/8BND SOC S40

**MSRP:** 2352.34

**Part Code:** 390

**Weight(lbs):** 97.775

**Weight(kg):** 44.35

**Weight(gm):** 44350


**Size:** 16 X 14

**Color:** WHITE

**Material:** PVC

**Schedule** SCH 40 DWV- Reducing

**Connection** Socket x Socket x Socket



**G1** = 1

**G2** = 28-3/4

**G3** = 30-1/4

**H** = 37-1/4

**L** = 44-3/4

**M** = 17

**M1** = 14-7/8

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

