

**Part No:** 3792-532

**Fabricated DWV**

**Double Wye**

**Desc:** 6X4 PVC RED DBL COMB Y&1/8 BND SOC SCH40

**MSRP:** 270.31

**Part Code:** 390

**Weight(lbs):** 10.472


**Weight(kg):** 4.75

**Weight(gm):** 4750

**Size:** 6"X6"X4"X4"

**Color:** WHITE

**Material:** PVC



**Schedule** SCH 40 DWV

**Type** Reducing Double Combo Wye  
With 1/8 Bend

**Connection** Socket x Socket x Socket x Socket

**G1** = 1/16

**G2** = 11-11/16

**L** = 18-1/4

**M** = 7-3/16

**M1** = 5-1/16

**G3** = 11-5/16

**H1** = 13-1/16

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

