

Part No: 3901-578

Fabricated DWV

Tees

Desc: 8X2 PVC REDUCING TEE SOC SCH80

MSRP: 337.46

Part Code: 400

Weight(lbs): 12.893


Weight(kg): 5.848

Weight(gm): 5848

Size: 8 X 2

Color: GRAY

Material: PVC



Type Reducing Vent Tee
Schedule SCH 80 DWV
Connection Socket x Socket x Socket

G = 4-11/16

G1 = 6-1/8

H = 8-15/16

H1 = 7-7/8

L = 17-7/8

M = 9-5/8

M1 = 2-13/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

