

**Part No:** 3901-904

**Fabricated DWV**

**Tees**

**Desc:** 24X4 PVC RED TEE SOC SCH80

**MSRP:** 3184.73

**Part Code:** 400

**Weight(lbs):** 220.198


**Weight(kg):** 99.88

**Weight(gm):** 99880

**Size:** 24 X 4

**Color:** GRAY

**Material:** PVC



**Type** Reducing Vent Tee  
**Schedule** SCH 80 DWV  
**Connection** Socket x Socket x Socket

**H** = 21

**H1** = 16-15/16

**L** = 42

**M** = 26-7/16

**M1** = 5-3/16

**G** = 9

**G1** = 14-11/16

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

