

Part No: 3901-914

Fabricated DWV

Tees

Desc: 24X14 PVC RED TEE SOC SCH80

MSRP: 4932.46

Part Code: 400

Weight(lbs): 285.406


Weight(kg): 129.458

Weight(gm): 129458

Size: 24 X 14

Color: GRAY

Material: PVC



Type Reducing Vent Tee
Schedule SCH 80 DWV
Connection Socket x Socket x Socket

G = 13-1/4

G1 = 16-5/16

H = 25-1/4

H1 = 23-5/16

L = 50-1/2

M = 26-7/16

M1 = 15-1/2

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

