

**Part No:** 3920-100

**Fabricated DWV**

**Crosses**

**Desc:** 10 PVC CROSS SOC SCH80

**MSRP:** 1435.56

**Part Code:** 400

**Weight(lbs):** 51.487

**Weight(kg):** 23.354

**Weight(gm):** 23354

**Size:** 10


**Color:** GRAY

**Material:** PVC

**Type** Standard

**Schedule** SCH 80 DWV

**Connection** Soc x Soc x Soc x Soc



**H1** = 14-1/4

**H** = 14-1/4

**G1** = 9

**G** = 9

**L** = 28-1/2

**L1** = 28-1/2

**M** = 11-15/16

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/4$  & larger  $\pm 1/2$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses;  $\pm 1/4$  inch.; wyes  $\pm 1/2$  inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/4$  inch; 14" & larger  $\pm 1/2$  inch.

**L** = Overall length of fittings;  $\pm 1/2$  inch; wyes  $\pm 1$  inch; 14" & larger  $\pm 1$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/4$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/2$  inch.

**W** = Height of cap;  $\pm 1/4$  inch.

## Typical Fabricated Dimension References

