

Part No: 4433I-080P

Valves

Industrial Swing Check Valve

Desc: 8 PP SWING CHECK VALVE FLANGED FKM W/IND

MSRP: 17255.71

Part Code: 112

Weight(lbs): 57.475

Weight(kg): 26.07

Weight(gm): 26070

Size: 8"


Color: BEIGE

Material: Polypropylene

Type W/Indicator

O-Ring FKM

Pressure Rating 70 PSI @ 73° F



A = 19- 1/8

B = 19-23/32

C = 13- 1/2

D = 7- 7/8

E = 11- 5/8

F = 16- 5/16

Cv = 1900
Values

No of = 8
Bolts

Bolt = 11- 3/4
Circle
Dia.

Bolt Size = 7/8

I = 1- 5/32

G = 7- 3/4

H = 6- 1/2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch


L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References



The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained therefrom. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006