

Part No: 5223-020C

Valves

Plug Gate Valve

Desc: 2 CPVC PLUG GATE VALVE FLANGED EPDM

MSRP: 1199.79

Part Code: 202

Weight(lbs): 4.213


Weight(kg): 1.911

Weight(gm): 1911

Size: 2"

Color: GRAY

Material: CPVC



D = 7- 1/8

E = 3- 7/16

F = 5-15/16

G = 4- 5/32

Type Plug Gate
Connection Flange x Flange
O-Ring EPDM
Pressure Rating 150 psi @ 73° F

Injection Molded Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.
- H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch
- L** = Overall length of fittings; ± 1/16 inch.
- M** = Outside diameter of socket/thread hub; ± 1/16 inch.
- N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.
- W** = Height of cap; ± 1/16 inch

Typical Molded Dimension References

