

Part No: 5807-01510

Swing Joints

Riser Assemblies

Desc: 1-1/2 PVC SWING JNT RSR W/10 NIP MPTXMPT

MSRP: 147.87

Part Code: 030

Weight(lbs): 2.784

Weight(kg): 1.263

Weight(gm): 1263

Size: 1-1/2"

Color: BLUE

Material: PVC

Inlet Mipt

Outlet Mipt

Riser Type Buttress Thread

Type Standard

Riser Nipple Length 10

A = 10

B = 12- 7/16

C = 15- 1/4

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch


L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References



The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained therefrom. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006